

<b>1.</b> Device Name	<b>NITRILE BLUES PF</b>																																									
<b>2.</b> Description	Powder Free Nitrile, Non Medical Grade, On-Line Chlorinated, Textured Surface, Beaded Cuff, Ambidextrous, Non Sterile, Free from Vinyl, BPA, phthalates and MBT, Single Use.																																									
<b>3.</b> Product Codes & Sizes	<table border="1"> <thead> <tr> <th>Product Code</th> <th>Size</th> <th>Inner Barcode</th> <th>Shipper Barcode</th> </tr> </thead> <tbody> <tr> <td>41060</td> <td>SMALL</td> <td>9311059410605</td> <td>19311059410602</td> </tr> <tr> <td>41061</td> <td>MEDIUM</td> <td>9311059410612</td> <td>19311059410619</td> </tr> <tr> <td>41062</td> <td>LARGE</td> <td>9311059410629</td> <td>19311059410626</td> </tr> <tr> <td>41063</td> <td>XL</td> <td>9311059410636</td> <td>19311059410633</td> </tr> </tbody> </table>				Product Code	Size	Inner Barcode	Shipper Barcode	41060	SMALL	9311059410605	19311059410602	41061	MEDIUM	9311059410612	19311059410619	41062	LARGE	9311059410629	19311059410626	41063	XL	9311059410636	19311059410633																		
Product Code	Size	Inner Barcode	Shipper Barcode																																							
41060	SMALL	9311059410605	19311059410602																																							
41061	MEDIUM	9311059410612	19311059410619																																							
41062	LARGE	9311059410629	19311059410626																																							
41063	XL	9311059410636	19311059410633																																							
<b>4.</b> Recommended Applications	<ul style="list-style-type: none"> <li>Food Processing</li> <li>Food Service</li> <li>Food Manufacturing</li> <li>Cafes</li> <li>Cleaning</li> <li>Industrial</li> <li>Cosmetic</li> <li>Hair and Beauty</li> <li>Childcare</li> <li>Aged Care</li> <li>Tattooists</li> <li>Abattoirs &amp; Meatworks</li> <li>Car Industry</li> <li>Maintenance</li> </ul>																																									
<b>5.</b> Materials	Nitrile, Potassium Hydroxide, Aquawax, ZDBC, ZDEC, Zinc Oxide, Wingstay-L, Sulphur, Titanium Dioxide, Blue pigment.																																									
<b>6.</b> Production Process	Former cleaning and washing, coagulant dipping, coagulant drying, Nitrile dipping, Nitrile drying oven, beading, leaching tank dip, main curing oven, cooling tank, chlorination tank, soak rinse tank, neutralizer, post rinsing tank, pre drying oven, stripping, QC inspection, tumbling, packing, Pre-shipment inspection.																																									
<b>7.</b> Standards & Approvals	<div style="display: flex; align-items: center;"> <p> <b>Nitrile Blues PF</b> are tested to and complies with;           <ul style="list-style-type: none"> <li>ASTM D6319-00</li> <li>Certified under HACCP Food Safety Accreditation</li> </ul> </p> </div>																																									
<b>8.</b> Dimensions	<table border="1"> <thead> <tr> <th>SIZE</th> <th>WEIGHT p/pc +0.0- 0.2gm</th> <th>LENGTH (min)</th> <th>THICKNESS FINGER SINGLE WALL (+/-0.03mm)</th> <th>THICKNESS PALM SINGLE WALL (+/-0.03mm)</th> <th>THICKNESS CUFF SINGLE WALL</th> <th>PALM WIDTH (+/-3)</th> </tr> </thead> <tbody> <tr> <td>SMALL</td> <td>4.0gm</td> <td>240mm</td> <td>0.12mm</td> <td>0.10mm</td> <td>0.08mm</td> <td>84mm</td> </tr> <tr> <td>MEDIUM</td> <td>4.4gm</td> <td>240mm</td> <td>0.12mm</td> <td>0.10mm</td> <td>0.08mm</td> <td>94mm</td> </tr> <tr> <td>LARGE</td> <td>4.9gm</td> <td>240mm</td> <td>0.12mm</td> <td>0.10mm</td> <td>0.08mm</td> <td>105mm</td> </tr> <tr> <td>XL</td> <td>5.5gm</td> <td>240mm</td> <td>0.12mm</td> <td>0.10mm</td> <td>0.08mm</td> <td>113mm</td> </tr> </tbody> </table>							SIZE	WEIGHT p/pc +0.0- 0.2gm	LENGTH (min)	THICKNESS FINGER SINGLE WALL (+/-0.03mm)	THICKNESS PALM SINGLE WALL (+/-0.03mm)	THICKNESS CUFF SINGLE WALL	PALM WIDTH (+/-3)	SMALL	4.0gm	240mm	0.12mm	0.10mm	0.08mm	84mm	MEDIUM	4.4gm	240mm	0.12mm	0.10mm	0.08mm	94mm	LARGE	4.9gm	240mm	0.12mm	0.10mm	0.08mm	105mm	XL	5.5gm	240mm	0.12mm	0.10mm	0.08mm	113mm
SIZE	WEIGHT p/pc +0.0- 0.2gm	LENGTH (min)	THICKNESS FINGER SINGLE WALL (+/-0.03mm)	THICKNESS PALM SINGLE WALL (+/-0.03mm)	THICKNESS CUFF SINGLE WALL	PALM WIDTH (+/-3)																																				
SMALL	4.0gm	240mm	0.12mm	0.10mm	0.08mm	84mm																																				
MEDIUM	4.4gm	240mm	0.12mm	0.10mm	0.08mm	94mm																																				
LARGE	4.9gm	240mm	0.12mm	0.10mm	0.08mm	105mm																																				
XL	5.5gm	240mm	0.12mm	0.10mm	0.08mm	113mm																																				
<b>9.</b> Physical Properties	<table border="1"> <thead> <tr> <th>DESCRIPTION</th> <th>BEFORE AGEING</th> <th>AFTER AGEING</th> </tr> </thead> <tbody> <tr> <td>Elongation at break (%)</td> <td>500 minimum</td> <td>500 minimum</td> </tr> <tr> <td>Tensile Strength (MPa)</td> <td>14 minimum</td> <td>14 minimum</td> </tr> </tbody> </table> <p><i>Note: if Textured gloves then minimum requirements shall be 10% lower than those shown in table.</i></p>							DESCRIPTION	BEFORE AGEING	AFTER AGEING	Elongation at break (%)	500 minimum	500 minimum	Tensile Strength (MPa)	14 minimum	14 minimum																										
DESCRIPTION	BEFORE AGEING	AFTER AGEING																																								
Elongation at break (%)	500 minimum	500 minimum																																								
Tensile Strength (MPa)	14 minimum	14 minimum																																								
<b>10.</b> Colour	Blue																																									



**11. Performance Requirements**

Gloves shall be sampled and inspected in accordance with ISO 2859-1. The inspection levels and acceptable quality limits (AQLs) shall conform to those listed in below table for the characteristics listed.

CHARACTERISTICS	INSPECTION LEVEL	ACCEPTABLE QUALITY LEVEL	REFERENCE STANDARD
Dimensions	S2	4.0	ASTM D6319-00
Physical Properties	S2	4.0	ASTM D6319-00
Watertightness	G1	4.0	ASTM D6319-00
Visual Defects: Major Minor	G1	4.0 6.5	Manufacturers Practice

Notes: For Dimensions and Physical Properties a median of 13 test pieces used as per EN455-02-00

**12. Quality Control Inspection Procedures**

- a) Shipment is placed in quarantine area separately from other gloves in warehouse as one lot
- b) Shipment is then sorted by sizes if shipment consists of more than one size.
- c) QC inspector records lot number(s) indicated on inner boxes and outer cases, sizes quantity of shipment, buyer, date, etc
- d) QC inspector selects at random samples according to ISO procedures for sampling, each lots of different sizes are handled separately
- e) Samples are sent for testing as per requirements
- f) Results of tests will be recorded and only those that meet acceptance criteria are released for dispatch. If shipment consists of more than one size, shipment will be released only when all lots of different sizes have passed.
- g) If a shipment is found to fail test requirements it will be rejected by QC inspector and not released for shipment.

**13. Packaging**

100 pieces will be packed into a dispenser box. The number contained in each dispenser box determined by weight. 10 dispenser boxes are packed in 2 layers of 5 giving 10 dispenser boxes inside export quality shipper carton (outer).

**14. Shipper Carton Specifications**

SIZE	LENGTH (mm)	WIDTH (mm)	HEIGHT (mm)	GROSS WEIGHT (kg)
SMALL	370	258	245	5.0
MEDIUM	370	258	245	5.4
LARGE	370	258	245	5.9
XL	370	258	245	6.5

**15. Storage Conditions**

The gloves will maintain their properties when stored in dry conditions out of direct sunlight at between 10°C to 30°C.

**16. Shelf Life**

The gloves shall have a shelf life of 5 years from the date of manufacture when stored in compliance with the above storage conditions.