


1. Device Name	ECOCLEAR																																								
2. Description	Powder Free Vinyl, Non Medical Grade, Beaded Cuff, Ambidextrous, Non Sterile, Does not contain DOP, DEHP, DBP, DIDP phthalates, Single Use.																																								
3. Product Codes & Sizes	<table border="1"> <thead> <tr> <th>Product Code</th> <th>Size</th> <th>Inner Barcode</th> <th>Shipper Barcode</th> </tr> </thead> <tbody> <tr> <td>41120</td> <td>SMALL</td> <td>9311059411206</td> <td>19311059411203</td> </tr> <tr> <td>41121</td> <td>MEDIUM</td> <td>9311059411213</td> <td>19311059411210</td> </tr> <tr> <td>41122</td> <td>LARGE</td> <td>9311059411220</td> <td>19311059411227</td> </tr> <tr> <td>41123</td> <td>XL</td> <td>9311059411237</td> <td>19311059411234</td> </tr> </tbody> </table>				Product Code	Size	Inner Barcode	Shipper Barcode	41120	SMALL	9311059411206	19311059411203	41121	MEDIUM	9311059411213	19311059411210	41122	LARGE	9311059411220	19311059411227	41123	XL	9311059411237	19311059411234																	
Product Code	Size	Inner Barcode	Shipper Barcode																																						
41120	SMALL	9311059411206	19311059411203																																						
41121	MEDIUM	9311059411213	19311059411210																																						
41122	LARGE	9311059411220	19311059411227																																						
41123	XL	9311059411237	19311059411234																																						
4. Recommended Applications	<ul style="list-style-type: none"> Food Manufacturing Food Processing Food Service Cafes Cleaning Industrial Cosmetic Hair and Beauty Childcare Tattooists Abattoirs & Meatworks 																																								
5. Materials	Polyvinyl Chloride Resin, Calcium-Zinc Stabilizer, Bis(2-ethylhexyl) terephthalate (DOTP), Polyurethane.																																								
6. Production Process	Raw material inspection, PVC mixing and preparation, Laboratory test of compounded PVC solution, Dip Line process, QC in process inspection, Tumbling, QC off-line inspection, Packing, Packing process inspection, QC Pre-shipment inspection, Ship.																																								
7. Standards & Approvals	<div style="display: flex; align-items: center;">  <p>EcoClear is tested to and complies with;</p> <ul style="list-style-type: none"> Certified under HACCP Food Safety Accreditation Tested and complied in accordance with European Commission Regulation (EU) No. 2020/1245 and (EU) No. 10/2011 on plastic materials and articles intended to come in contact with food. </div>																																								
8. Dimensions	<table border="1"> <thead> <tr> <th>SIZE</th> <th>WEIGHT p/pc +0.3- 0.3gm</th> <th>LENGTH (min)</th> <th>THICKNESS FINGER SINGLE WALL (+/-0.03)</th> <th>THICKNESS PALM SINGLE WALL (+/-0.03)</th> <th>THICKNESS CUFF SINGLE WALL (+/-0.03)</th> <th>PALM WIDTH (+/-5)</th> </tr> </thead> <tbody> <tr> <td>SMALL</td> <td>4.0gm</td> <td>230mm</td> <td>0.11mm</td> <td>0.09mm</td> <td>0.07mm</td> <td>85mm</td> </tr> <tr> <td>MEDIUM</td> <td>4.5gm</td> <td>230mm</td> <td>0.11mm</td> <td>0.09mm</td> <td>0.07mm</td> <td>95mm</td> </tr> <tr> <td>LARGE</td> <td>5.0gm</td> <td>230mm</td> <td>0.11mm</td> <td>0.09mm</td> <td>0.07mm</td> <td>105mm</td> </tr> <tr> <td>XL</td> <td>5.5gm</td> <td>230mm</td> <td>0.11mm</td> <td>0.09mm</td> <td>0.07mm</td> <td>115mm</td> </tr> </tbody> </table>						SIZE	WEIGHT p/pc +0.3- 0.3gm	LENGTH (min)	THICKNESS FINGER SINGLE WALL (+/-0.03)	THICKNESS PALM SINGLE WALL (+/-0.03)	THICKNESS CUFF SINGLE WALL (+/-0.03)	PALM WIDTH (+/-5)	SMALL	4.0gm	230mm	0.11mm	0.09mm	0.07mm	85mm	MEDIUM	4.5gm	230mm	0.11mm	0.09mm	0.07mm	95mm	LARGE	5.0gm	230mm	0.11mm	0.09mm	0.07mm	105mm	XL	5.5gm	230mm	0.11mm	0.09mm	0.07mm	115mm
SIZE	WEIGHT p/pc +0.3- 0.3gm	LENGTH (min)	THICKNESS FINGER SINGLE WALL (+/-0.03)	THICKNESS PALM SINGLE WALL (+/-0.03)	THICKNESS CUFF SINGLE WALL (+/-0.03)	PALM WIDTH (+/-5)																																			
SMALL	4.0gm	230mm	0.11mm	0.09mm	0.07mm	85mm																																			
MEDIUM	4.5gm	230mm	0.11mm	0.09mm	0.07mm	95mm																																			
LARGE	5.0gm	230mm	0.11mm	0.09mm	0.07mm	105mm																																			
XL	5.5gm	230mm	0.11mm	0.09mm	0.07mm	115mm																																			
9. Physical Properties	<table border="1"> <thead> <tr> <th>DESCRIPTION</th> <th>BEFORE AGEING</th> <th>AFTER AGEING</th> </tr> </thead> <tbody> <tr> <td>Elongation at break (%)</td> <td>400</td> <td>350</td> </tr> <tr> <td>Tensile Strength (MPa)</td> <td>14</td> <td>14</td> </tr> </tbody> </table>						DESCRIPTION	BEFORE AGEING	AFTER AGEING	Elongation at break (%)	400	350	Tensile Strength (MPa)	14	14																										
DESCRIPTION	BEFORE AGEING	AFTER AGEING																																							
Elongation at break (%)	400	350																																							
Tensile Strength (MPa)	14	14																																							
10. Colour	Clear																																								



**12.
Quality
Control
Inspection
Procedures**

- a) Shipment is placed in quarantine area separately from other gloves in warehouse as one lot
- b) Shipment is then sorted by sizes if shipment consists of more than one size.
- c) QC inspector records lot number(s) indicated on inner boxes and outer cases, sizes quantity of shipment, buyer, date, etc
- d) QC inspector selects at random samples according to ISO procedures for sampling, each lots of different sizes are handled separately
- e) Samples are sent for testing as per requirements
- f) Results of tests will be recorded and only those that meet acceptance criteria are released for dispatch. If shipment consists of more than one size, shipment will be released only when all lots of different sizes have passed.
- g) If a shipment is found to fail test requirements it will be rejected by QC inspector and not released for shipment.

**13.
Packaging**

100 pieces will be packed into a dispenser box. The number contained in each dispenser box determined by weight. 10 dispenser boxes are packed in 2 layers of 5 giving 10 dispenser boxes inside export quality shipper carton (outer).

**14.
Shipper
Carton
Specifications**

SIZE	LENGTH (mm)	WIDTH (mm)	HEIGHT (mm)	GROSS WEIGHT (kg)
SMALL	315	240	240	5.0
MEDIUM	315	240	240	5.5
LARGE	315	240	240	6.0
XL	315	240	240	6.5

**15.
Storage
Conditions**

Store in a cool, dry and ventilated area.
Do not store above 37°C. Keep away from heat. Shield open boxes from direct sunlight, fluorescent lighting and x-ray. Improper storage will decrease shelf life.

**16.
Shelf Life**

The gloves shall have a shelf life of 3 years from the date of manufacture when stored in compliance with the above storage conditions.